## Axicon 6015 Barcode Verifier

# **BXICOU**

## THE BARCODE EXPERTS

#### Axicon 6015 Barcode Verifier

#### **Product Summary**

Independently tested & certified to meet International Standards, the Axicon 6015 has been specifically designed to read all linear barcodes with a width of up to 66mm (2.6") including quiet zones. The system consists of a state of the art CCD read head and application software. Our development program means that not only will your verifier always meet the latest ISO/ ANSI standard, but also a wide range of application standards including GS1-128 & ISBN/ISSN. An extensive array of additional reporting tools is also provided with every verifier.

#### **Typical Application**

Smaller barcodes including all retail point of sale barcodes whether printed on labels, flexible packaging, cartons, bags, cans or jars.

#### Installation

the leading edge.

Simply install the software on your computer, plug in the verifier and you can be confident that your barcodes are being checked to the highest standards. The standard software includes everything you could ever need from a barcode verifier. Traceability features include automatic saving of files, reports in a variety of formats, data content checks against a wide range of application standards as well as the product look-up function - helping you to ensure that your barcodes are fit for purpose.

The Axicon Verifier, when used in conjunction with the accurately produced calibration sheet, forms an integral part of your ISO 9000 quality control procedures. Free software updates are downloadable from our website www.axicon.com,

ensuring that your verifier will remain at

Accuracy, Repeatability and Reliability. Axicon has been involved with barcode verification for 30 years and pioneered the use of CCD imaging for verification. With time comes experience and insight and we're not short of either! Actively listening to our clients suggestions, we constantly enhance and improve our system. The result? The most comprehensive and flexible verification system on the market.

### Benefits

- ISO/ANSI Verification Standards
- Automatic variable aperture
- Static Scan Reflectance Measurement
- Al Data Content Checker (For GS1-128 & GS1 DataBar etc.)
- Multi Language User Interface
- Wide range of "plug-ins" for additional features.
- USB Connectivity
- Automatic Calibration Reminder









SOFTWARE SPECIFICATIONS

GS1 SYMBOLOGIES: EAN-8, EAN-13 (with or without addons), ITF-14/Case Code, GS1-DataBar (all symbologies), GS1-128, UPC-A, UPC-E Symbologies Verified:

(with or without addons). (Subject to length of barcode)

OTHER SYMBOLOGIES: Code 39, Code 93, Code 128, Codabar, ITF, MSI Plessey, Pharmacode (Laetus: optional extra)

AIAG, Belgian Pharmacode (MSI), Belgian Pharmacode (Unique), CIP39, Coupon Codes (UK, USA, Euro), Code Vignette, GS1 AI Check, HIBC, ISBN/ISSN, Italian Pharmacode (IMH), LPPR, M&S, PZN, SISAC, Variable Measure Codes (Branded, Instore, Australian). Application

Standards:

Analysis Performed on Relevant Symbologies:

Full ISO/ANSI Parameter Analysis (Rmin, Rmax, Global Threshold, Symbol Contrast, Min Edge Contrast, Modulation, Defects, Decodability, Decode), Decodability per Symbol Character, Average Bar Gain, Check Digit Validation, Data Length, Nominal Bar Width Analysis (X Dimension), Print Contrast Measurement (PCS), Symbol Structure including Parity, Subsets & Start/Stop Characters, Quiet Zone Validation, Wide to Narrow Ratio Display and Validation.

Diagnostics Windows: Parameter Detail Results, Dimensional Analysis, Pass/Fail, Scan Reflectance Profile, Static Scan Reflectance, Summary, Traditional

Results, Application Identifier Data Content Checker (for GS1-128, GS1-DataBar), Product-Look-Up.

Logging: Scan Saving and Loading - stores complete details of scan file data. Allows for remote diagnostics and also for increased traceability.

Calibration Logging: A record of date and time to show when the hardware has been calibrated is kept - vital for ISO 9000 records

Audible Warnings, Calibration Expiry Warning, Changeable Pass / Fail and Warning Colours, Optional Check Digit Validation (Code 39, Configurable Options:

Codabar, ITF), File Saving, Multi-Scan Averaging, Pass Grade, Print Options, Window Sizes and Positions.

Error Messages: Check Digit Error, Data Content Error, Incorrect Wide to Narrow Ratio, Print Quality Failure, Product Look-Up Error, Quiet Zone Error,

Reference Decode Algorithm Error, Structure Error, X Dimension Range Checking

Code 39 full ASCII, CSV File Saving, Gen Spec, Job Reference, Product Lookup, Text Lookup, Time Zone, UPC, User Data, User Name, (see Plugins Available:

also Application Standards) - and many others

Additional Software: Pharmacode (Laetus) - Decode and Analysis of Laetus Pharmacode. (Chargeable optional extra)

ScanDB - Reporting Tool transferring data from saved scans into a .csv file

RepGen - Configurable report generation tool

#### HARDWARE SPECIFICATIONS

Dimensions: 165 x 75 (50) x 128 mm (6.4" x 2.9" (2") x 5"), Scan Width - 66mm (2,6") (including quiet zones)

Weight: 250g (8.82oz) ABS plastic Construction: USB Interface:

Current draw 130mA - supplied from USB host. Power Consumption:

Nominal Measuring aperture

3mil, 5mil, 6mil, 10mil and 20mil.

The software automatically identifies the symbology/nominal bar size (X dimension) and adjusts the aperture size in order to comply with

the symbology specifications and International Standards.

Wavelength of Light: 660 nanometers

#### GENERAL INFORMATION

Environmental:

Print of Analysis: A printed report can be produced on any connected windows printer. The report will be automatically resized to suit the output media.

Printouts can be produced for the main verification information (including: Decoded Number, Time & Date, Number of Scans, Code Type, Average ISO/ANSI Grade, Average Bar Gain, Magnification, Check Character, Quiet Zone & Individual Parameters) Scan Reflectance Profiles, Dimensional Analysis, also for GS1-128 & GS1-DataBar Data Content information and Plugin Results.

GS1 Verification Template supported

Customised reports available via RepGen and ScanDB utilities.

Standard Accessories: Transit Case, Calibration Sheet, Start-up Guide, Software CD, Compliance Certificates.

System Requirements: PC running a currently supported version of Windows

> Operating Temperature: 10° to 40°C Storage Temperature: -20° to 70°C

Relative Humidity: 25% to 80% @ 40°C non-condensing

Regulatory Approvals CE Certified, ROSH Compliant.

Meets ISO 15416 and 15426-1 standards

Has all the features necessary to meet the requirements of 21 CFR part 11.

Warranty: 2 years parts and labour - return to bench.

All trademarks are acknowledged as belonging to their respective companies.

Due to Axicon's continuing product improvement programs, specifications and features herein are subject to change without notice.





